


CACHN 10XIPC UPLFLN-IPC / CACHN-IPC / LCACHN-IPC




This series is used in combination with the pre-centered phase contrast slider CKX3-SLP. When changing the objective magnification in phase contrast observation, no centering adjustment is necessary.

Specifications

opecinications	
Numerical Aperture (NA)	0.25
Working distance (W.D.) (mm)	8.8
Field Number (FN)	22
Cover Glass Thickness (mm)	1
Immersion	-
Spring	-
Correction Collar	-
Iris Diaphragm	-
Waterproof & Oil proof function	-
Ultra Wide anti-reflection coating	-
Super apochromatic	-
Brightfield	Good
Darkfield	Good
DIC	N/A
Phase Contrast	Excellent
Relief Contrast	N/A
Polarized Light	Limitation
Fluorescence (B, G Excitation)	Good
UV Fluorescence (at 365nm)	N/A
IR DIC	N/A
Multi photon excitation	N/A
	·

CACHN 10XIPC

Dimension



• Specifications and appearances are subject to change without any notice or obligation on the part of the manufacturer.

